



Applicable Requirements :
ANSI/UL 1017
CSA C22.2 No.243

Characteristics



Cleanroom
Compatible




Pharma
Applications



HEPA -
Included



High Filtration
Efficiency Unit



Accessories
Included



Activated
Carbon



Wet and Dry
Recovery



Mercury
Recovery



- HEPA filter with an efficiency of 99.995% at 0.3 micron. Tested IEST-RP-CC001. H14 by MPPS method as per EN 1822 and OSHA compliant. All of our HEPA vacuum systems are aerosol leak tested before leaving our facility - included
- Cleanroom compatible with ISO Class 4 (former Class 10). Can be used in the Pharmaceutical industry
- Designed for mercury recovery
- Heavy duty 2-stage by-pass motor
- For wet & dry recovery
- Polyethylene recovery tank
- EMI/RFI Shielded
- Timer (hour counter) included
- Includes Mersorb® brand carbon for the adsorption of mercury vapors
- Includes a suction hose, mercury separator and jars with lids
- Mounted on a 4-wheel dolly for easy maneuverability

Specifications

MRV-15 ELEC (STD)	110805A
Model Name	MRV-15 ELEC (STD)
Type (Powerhead)	Electric
Tension	120 V
Frequency	60 Hz
Phase	Single
Wattage	1050 W
Power	1.6 HP
Amperage	10.5 A
Air Flow	110 CFM
Vacuum Pressure	107 " H ₂ O
Sound Level	70 dB(A)
Type of Power Outlet	120V
Suction Inlet	1.5 "
Cart Type	4 Wheel Dolly (4W)
Filter Cleaning	None
Dust Recovery Tank	10 gal.
Dry Recovery - Disposable Filter Bag	5 gal.
Liquid Recovery Capacity	10 gal.
Length	18 "
Width	24 "
Height	48 "
Weight (Vacuum Only)	92 lb.
Cord Length	35 ft.

Please note that specifications are subject to change without notice

Use only recommended tools & accessories



HEPA Filter - Included




Activated Carbon Cartridge for Mercury Recovery - Included



Hour Counter for MRV models - Included



Mercury Recovery Separator with Jar - Included



MRV-15/16 Tools and Accessories - Included



Clear Suction Hose Assembly for use with Mercury Separator - Included



Jar for Mercury Recovery, 20 oz (540 ml) with lid - Optional

U.S. Headquarters

Tiger-Vac Inc.
11 SW 12th Ave #112
Dania, FL 33004
USA

Tel: 1-800-668-4437 (954-925-3625)
Fax: 1-800-668-4439 (954-925-3626)
Website: <http://www.tiger-vac.com>
Email: sales@tiger-vac.com

International Headquarters

Tiger-Vac International Inc.
2020 Dagenais Blvd. Ouest
Laval, Quebec
Canada H7L 5W2

Tel: (450-625-0099)
Fax: (450-625-3388)
Website: <http://www.tiger-vac.com>
Email: sales@tiger-vac.com



Applicable Requirements :
ANSI/UL 1017
CSA C22.2 No.243



Cleanroom
Compatible



Pharma
Applications



HEPA -
Included



High Filtration
Efficiency Unit



Accessories
Included



Activated
Carbon



Wet and Dry
Recovery



Mercury
Recovery

Specifications For MRV-15 ELEC (STD)

Name	Part Number	Tension	Frequency	Phase	Wattage	Power	Amperage	Air Flow	Vacuum Pressure	Type of Power Outlet	Dust Recovery Tank	Dry Recovery - Disposable Filter Bag
MRV-15 ELEC (STD)	110805A	120 V	60 Hz	Single	1050 W	1.6 HP	10.5 A	110 CFM	107 " H ₂ O	120V	10 gal.	5 gal.
	Dimensions: H48" x W24" x L18"		Weight: 92 lb.		Sound Level: 70 dB(A)							
Description: Manufacturer motor performance only on an orifice of Ø2" (Ø50mm). Results may vary.												

Please note that specifications are subject to change without notice

Technical Sheet For MRV-15 ELEC (STD)

HEPA FILTER AND ACCESSORIES - Included

Part #	Description
211027B	HEPA FILTER 99.995% EFFICIENCY ON 0.3 MICRON (CE VERSION)

FILTERS AND ACCESSORIES - Included

Part #	Description
211305	DOUBLE CLOTH FILTER ASSEMBLY
211394	LIQUID FILTER ASSEMBLY

ACTIVATED CARBON CARTRIDGE - Included

Part #	Description
212200C	CARBON CARTRIDGE ASSEMBLY WITH 3mm MERSORB ACTIVATED CARBON (FOR MERCURY VAPORS)

ACTIVATED CARBON CARTRIDGE - Optional

Part #	Description
212200B	CARBON CARTRIDGE ASSEMBLY WITH 3mm CARBON (REGULAR)
212200K	CARBON CARTRIDGE ASSEMBLY WITH 3mm KOGC3/KINA3 CARBON (FOR CHLORIDE VAPORS)
212200L	CARBON CARTRIDGE ASSEMBLY WITH 3mm A-3 CARBON (FOR ARSINE AND PHOSPHINE VAPORS)

MERCURY RECOVERY SEPARATOR AND ACCESSORIES - Included

Part #	Description
212208	MERCURY SEPARATOR -STAINLESS STEEL(INCLUDES 2 MERCURY RECOVERY JARS AND (2) LIDS FOR JAR)
212211	CLEAR SUCTION HOSE ASSEMBLY 1"(25.4mm)x8'(2.4m) FOR USE WITH MERCURY SEPARATOR

JAR FOR MERCURY RECOVERY - Optional

Part #	Description
212210	JAR FOR MERCURY RECOVERY 20oz(540 ml) WITH LID

POLY LINER RECOVERY BAGS AND ACCESSORIES - Included

Part #	Description
212368	POLY LINERS (PACKAGE OF 5)

DISPOSABLE FILTER BAGS - Included

Part #	Description
211063	PAPER FILTER BAGS (PACKAGE OF 5)
211845	PVC PIPE CONNECTOR FOR PAPER FILTER BAG FOR CWR-15 POLY TANK & MRV-15 (WITH 4 CRIMPS TO FIT ELBOW)

TOOLS AND ACCESSORIES - Included

Part #	Description
212215	CLEAR URETHANE SUCTION HOSE ASSEMBLY 10'(3m)WITH 1.5"(38mm) FEMALE CAMLOCK(PVC) ON ONE END
381092	DRAIN HOSE ASSEMBLY 0.75"(19mm)x5'(1.5m)CLEAR HOSE WITH 0.75"(19mm) PVC FEMALE CAMLOCK
381197	CREVICE TOOL, 11" (28cm), GREY PVC
381207	REDUCER/ADAPTOR Ø1.5"(38mm) TO Ø1.25"(32mm) -PVC
323312	ROUND BRUSH, Ø1.25"(32mm)
323314	UPHOLSTERY FLAT TOOL, Ø1.25"(32mm), PVC
381380	FLOOR TOOL 14" (36cm) ABS WITH NYLON BRUSHES
381381	FLOOR TOOL 14"(36cm) ABS w/SQUEEGEE RUBBER BLADES
381351A	WAND PVC DOUBLE BEND 54"(1.4m) WITH ABS AMERICAN ATTACHMENT